

Product sheet



MOSAIC™ LEGRAND

IP44 floor box for tile from 18 to 24mm with central cable exit

REF. 689623 | EAN. 3245066896236

> [Visit e-catalogue](#)

Product characteristics

- To be installed in back box Ref. 0 896 04
- Equipped with a central cable exit to be unscrewed, allowing the cover positioning when sockets are in use.
- Removable cover, possibly fitted with central cable exit
- For tile thickness from 18 to 24 mm
- To be equipped with 1 kit of vertical supports Ref. 6 896 57 for Arteur/Mosaic mechanism

Recommendation / Restriction

- For installation in concrete floor only - Attention no protection to water IP XX - Temperature of use, transport and storage: -5° à +60°

The product's benefits

Installation

- Provide a minimum height from 86 to 114mm maximum including 65 to 90 mm of concrete.

Usage

- Cleaning: do not use abrasive products or detergents.

Advantages

- Can be used as access trap. Floor box with one kit of vertical supports Ref. 6 896 57 for Arteur/Mosaic mechanism
- Allows the installation of different thicknesses of tiles and other coatings

Documentation

TECHNICAL DOCUMENTATION

→ LE06000AA-04.pdf | PDF (2.53Mo)

F02080EN-04.pdf | PDF (1.22Mo)

F02080FR-04.pdf | PDF (1.28Mo)

CAD & Design specs / BIM

Legrand-ip44-floor-boxes-EN.rfa | RFA (1.02Mo)

Legrand-boites-de-sol-ip44-FR.rfa | RFA (1.02Mo)

CATALOGUE PAGE & OTHERS

ex223001_1162.pdf | PDF (0.06Mo)

ex223001_1161.pdf | PDF (0.11Mo)