

Product sheet



LCS³ LEGRAND

Premium High-Density Jack (HDJ) RJ45 connectors category 6A UTP clarity black (set of 20)

REF. HDJ6A-00 | EAN. 0662875880837

Premium High-Density Jack (HDJ) from CAT5E to CAT 6A. Intertek ETL verified to TIA Category 5E, 6 & 6A component specification. To be installed in cassettes ref. 033680 and 033681 for patch panels

> [Visit e-catalogue](#)

Description

Premium High-Density Jack (HDJ) from CAT5E to CAT 6A. Intertek ETL verified to TIA Category 5E, 6 & 6A component specification. To be installed in cassettes ref. 033680 and 033681 for patch panels

Product characteristics

- RJ45 Cat 6A : Data rate up to 10 Gbps. This allows you to download a 1 Gigabyte file in 1 second.
- Black
- Rear - loading, 180° exit, 8 position
- Quick and easy lacing cap termination
- Set of 20 connectors

Recommendation / Restriction

- Conform to standards : ISO/IEC 11 801, EN 50173, ANSI/TIA-568-C.2, UL 1863 (HDJS references also UL 2043), IEEE 802.3af/802.3at 802.3bt. Type 1 to Type 4, FCC chapter 68, subchapter F and conform to IEC-603-7

Documentation

TECHNICAL DOCUMENTATION

 HDJ6A-00-Web-Cutsheet.pdf | PDF (0.05Mo)

Agreements & Certificates

 UL listed-UL-CA-L131600-33-22111102-6 | (0.22Mo)

 LGRP-00002-V03.01-EN.pdf | PDF (0.9Mo)

The product's benefits

Installation

- Quick and easy lacing cap termination : reduces wiring time for faster installations

Usage

- Accepts color ID icons: perfect for port identification or segmentation

CATALOGUE PAGE & OTHERS

 ex223001_0994.pdf | PDF (0.12Mo)