

# Product sheet



LCS<sup>3</sup> LEGRAND

Premium High-Density Jack (HDJ) RJ45 connectors category 6 STP clarity (set of 25)

REF. HDJS625 | EAN. 0662875020035

Premium High-Density Jack (HDJ) from CAT5E to CAT 6A. Intertek ETL verified to TIA Category 5E, 6 & 6A component specification. To be installed in cassettes ref. 033680 and 033681 for patch panels

> [Visit e-catalogue](#)

## Description

Premium High-Density Jack (HDJ) from CAT5E to CAT 6A. Intertek ETL verified to TIA Category 5E, 6 & 6A component specification. To be installed in cassettes ref. 033680 and 033681 for patch panels

### Product characteristics

- RJ45 Cat 6 : Data rate up to 1 Gbps. This allows you to download a 1 Gigabyte file in 8 seconds.
- All shielded
- Rear - loading, 180° exit, 8 position
- Quick and easy lacing cap termination
- Set of 25 connectors

### Recommendation / Restriction

- Conform to standards : ISO/IEC 11 801, EN 50173, ANSI/TIA-568-C.2, UL 1863 (HDJS references also UL 2043), IEEE 802.3af/802.3at 802.3bt. Type 1 to Type 4, FCC chapter 68, subchapter F and conform to IEC-603-7

## Documentation

### CATALOGUE PAGE & OTHERS

 [ex223001\\_0994.pdf](#) | PDF (0.12Mo)

## The product's benefits

### Installation

- Quick and easy lacing cap termination : reduces wiring time for faster installations

### Usage

- Accepts color ID icons: perfect for port identification or segmentation

### Agreements & Certificates

 [UL listed-UL-CA-L131600-33-22111102-6](#) | (0.22Mo)