

Product sheet



MOSAIC™ LEGRAND

Mosaic™ - RJ45 socket category 6A UTP 2 modules white

REF. 076574 | EAN. 3245060765743

> [Visit e-catalogue](#)

Product characteristics

- RJ45 Cat 6A : Data rate up to 10 GigaBit/s. This allows you to download a 1 GigaBytes file in 1 second.
- Support high capacity PoE applications. Power over Ethernet pass electric power along with data on twisted pair Ethernet cabling.
- Equipped with a transparent protective dust cover protecting the connector.
- 2 modules
- White

Recommendation / Restriction

- Conform to standards ISO/IEC 11801 Ed. 3.0, EN 50173-1 and TIA/EIA 568 C. Indoor use only.

The product's benefits

Installation

- Supplied with rocker plates, to be equipped with support frames and plates. Equipped with connectors with quick toolless connection.

Usage

- Suitable for commercial and residential installation. IP and analog phones. Very suitable for downloads, streaming or online games requiring low latency.

Avantages

- Toolless connector with fast connection thanks to integrated crimping.
- Compatible with cords equipped with RJ11, RJ12 or RJ45 plugs.
- Slot system allows a perfect and easy multigang setting. The support frames can be perfectly joined thereby easing the installation. Can be installed in a normal (single) flush mounting box, no need to additional wall groove cutting or cabling.

Documentation

TECHNICAL DOCUMENTATION

→ LE01557AK.pdf | PDF (1.59Mo)

F01436EN-02.pdf | PDF (2.27Mo)





Agreements & Certificates

LGRP-01330-V02.01-FR.pdf | PDF (0.81Mo)

CATALOGUE PAGE & OTHERS

ex223001_1188.pdf | PDF (0.12Mo)

ex223001_0981.pdf | PDF (0.11Mo)

-  LGRP-01330-V02.01-EN.pdf | PDF (0.82Mo)
-  LGRP-00420-V01.01-EN.pdf | PDF (0.63Mo)
-  AoC-CL2_Cat6A_UTP_32787_ac1171013 | (0.08Mo)
-  AoC-PL2_Cat6A_UTP_32787_ac1171012 | (0.08Mo)