

# Product sheet



SYNERGY™ LEGRAND

Synergy Authentic Telephone socket RJ11/RJ12  
Brushed Stainless steel

REF. 833054 | EAN. 3414970665027

> [Visit e-catalogue](#)

## Product characteristics

- RJ11/RJ12 single socket
- Screwless square cover plate 86x86mm
- Product thickness is 7mm (once is installed onto the wall).
- Brushed stainless steel : plate made of austenitic stainless steel, non magnetic, grade 304L
- Monobloc complete product = ready-to-install product

## Recommendation / Restriction

- For flush-mounting, back box to be minimum 35mm deep.  
Recommended inside use only

## Documentation

### CATALOGUE PAGE & OTHERS

 ex223001\_0723.pdf | PDF (0.11Mo)

## The product's benefits

### Installation

- Rapid cable connection

### Avantages

- Delivered with screws for flush & surface boxes in both plastic and metal boxes
- Made in UK