


Product sheet



SYNERGY™ LEGRAND

Sinergy Sleek 1 gang double data socket RJ45 category 6 Brushed Stainless steel

REF. 832057 | EAN. 3414970660862

> [Visit e-catalogue](#)

Product characteristics

- Category 6 UTP : data rate up to 1 GigaBit/s. This allows you to download a 1 GigaBytes file in 8 seconds.
- Screwless square cover plate 86x86mm
- Product thickness is 4mm (once is installed onto the wall).
- Brushed stainless steel : plate made of austenitic stainless steel, non magnetic, grade 304L
- Complete product, cover plates are clipped onto the mechanism itself.

Recommendation / Restriction

- For flush-mounting, back box to be minimum 35mm deep. Recommended inside use only

The product's benefits

Installation

- Rapid cable connection. Tool less connection

Usage

- Two connections in 1 gang

Avantages

- Delivered with screws for flush & surface boxes in both plastic and metal boxes
- Made in UK

Documentation

CATALOGUE PAGE & OTHERS

 ex223001_0730.pdf | PDF (0.09Mo)

Agreements & Certificates

-  AoC-PL2_C6_UTP_32886_ac1191056 | (0.06Mo)
-  AoC-PL3_Cat6_UTP_32754_ac1181026 | (0.07Mo)
-  AoC-CL4_Cat6_UTP_32866_ac1181047 | (0.08Mo)
-  AoC-Ac Delta Force 4PPoE 2019-677 | (0.08Mo)
-  AoC-SA51_SB51_ac109587 | (0.06Mo)
-  AoC-CL2_C6_UTP_32886_ac1191057 | (0.06Mo)
-  AoC-CL4_Cat6_UTP_32754_ac1181046 (| (0.08Mo)
-  AoC-CL2_Cat6UTP3275432861ac1181025 | (0.07Mo)
-  AoC-PL2_Cat6_UTP_32754_ac1181024 | (0.07Mo)