

Product sheet



SYNERGY™ LEGRAND

Synergy Authentic Data socket RJ45 category 6 Glossy gold

REF. 833456 | EAN. 3414970668363

> [Visit e-catalogue](#)

Product characteristics

- Category 6 UTP : data rate up to 1 GigaBit/s. This allows you to download a 1 GigaBytes file in 8 seconds.
- Screwless square cover plate 86x86mm
- Product thickness is 7mm (once is installed onto the wall).
- Glossy gold : plate made of stainless steel, grade 430, with a chromium plating which bring a better rusting resistance and a nicer finish
- Monobloc complete product = ready-to-install product

Recommendation / Restriction

- For flush-mounting, back box to be minimum 35mm deep. Recommended inside use only

Documentation

CATALOGUE PAGE & OTHERS

 [ex223001_0723.pdf](#) | PDF (0.11Mo)

The product's benefits

Installation

- Socket equipped with a tool less quick connector for intuitive and reliable wiring

Avantages

- Delivered with screws for flush & surface boxes in both plastic and metal boxes
- Made in UK

Agreements & Certificates

-  [AoC-PL2_C6_UTP_32886_ac1191056](#) | (0.06Mo)
-  [AoC-PL3_Cat6_UTP_32754_ac1181026](#) | (0.07Mo)
-  [AoC-CL4_Cat6_UTP_32866_ac1181047](#) | (0.08Mo)
-  [AoC-Ac Delta Force 4PPoE 2019-677](#) | (0.08Mo)
-  [AoC-SA51_SB51_ac109587](#) | (0.06Mo)
-  [AoC-CL2_C6_UTP_32886_ac1191057](#) | (0.06Mo)
-  [AoC-CL4_Cat6_UTP_32754_ac1181046](#) (| (0.08Mo)
-  [AoC-CL2_Cat6UTP3275432861ac1181025](#) | (0.07Mo)
-  [AoC-PL2_Cat6_UTP_32754_ac1181024](#) | (0.07Mo)