

Product sheet



HYPRA LEGRAND

Panel mounting socket inclined outlet Hypra-IP 44
-200/250 V~ -16 A -2P+E -metal

REF. 052032 | EAN. 3245060520328

> [Visit e-catalogue](#)

Product characteristics

- Hypra IP 44 sockets and plugs metal, plastic, rubber, IP 44/55 Prinsinter - LV 16 to 63 A and ELV 16 and 32 A - Conform to IEC 60309 - 1 and IEC 60309 - 2 - IP 44 according to IEC 60529 - IK 09 : plastic and rubber - IK 10 : metal according to IEC 62262 - Self - extinguishing : - 850°C (support of active parts) / 960 °C for Prinsinter) - 650 °C : plastic housing conform to IEC 60695 - 2 - 10 - 50°C to + 100°C (- 20°C for Prinsinter) LV panel mounting sockets 200 to 250 V~ 50/60 Hz - 16 A 2P+E - To be associated with box Cat.No 0 520 29 for surface - mounting socket or Cat.No 0 520 89 for through wiring surface mounting socket - Metal - 16 A

Documentation

TECHNICAL DOCUMENTATION

 F00138FR-04.pdf | PDF (1.44Mo)

 F00138EN-04.pdf | PDF (1.25Mo)

CAD & Design specs / BIM

LEGRAND_NON_INTERLOCKED_SOCKETS_FLUSH_MOUNTED_IP44_230.rfa | RFA (0.58Mo)

LEGRAND_PRISES_NON_VERROUILLEES_ENCASTREES_IP44_230.rfa | RFA (0.59Mo)

LEGRAND_PRISES_NON_VERROUILLEES_SAILLIES_IP44_230.rfa | RFA (0.7Mo)

 052032.dwg | DWG (0.13Mo)

LEGRAND_NON_INTERLOCKED_SOCKETS_SURFACE_MOUNTED_IP44_230.rfa | RFA (0.69Mo)

Agreements & Certificates

 OC / CB-FR_710635/A1 | (0.72Mo)