

Product sheet



P 17 TEMPRA LEGRAND

Panel mounting socket P17 - IP44 - straight outlet - 200/250 V~ - 32 A - 2P+E

REF. 058054 | EAN. 3245060580544

> [Visit e-catalogue](#)

Product characteristics

- P 17 Temptra Pro IP 44 - LV 16 and 32 A - sockets, plugs, mobile sockets, appliance inlets and interlocked switched sockets Panel mounting sockets straight outlet small flange - Can be fixed only on plain faceplates Cat.Nos 0 577 15/16200/250 V~ - IP 44 32 A - 2P+E

Documentation

TECHNICAL DOCUMENTATION

 F00142FR-02.pdf | PDF (1.39Mo)

 F00142EN-02.pdf | PDF (1.37Mo)

CAD & Design specs / BIM

No_interlocked_sockets_200_250V.rfa | RFA (1.42Mo)

Prises_non_verrouillées_200_250V.rfa | RFA (1.43Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0529.pdf | PDF (0.05Mo)

 ex223001_0525.pdf | PDF (0.12Mo)

 ex223001_0530.pdf | PDF (0.05Mo)

 ex223001_0531.pdf | PDF (0.06Mo)

Agreements & Certificates

 OC / CB-FR_702061 | (0.78Mo)