

Product sheet



DX³ LEGRAND

Motorized control DX3 24-48V for 1 module per pole devices up to 63A

REF. 406290 | EAN. 3245064062909

> [Visit e-catalogue](#)

Product characteristics

- Control voltage : 24 - 48V AC/DC
- 1 module wide

Recommendation / Restriction

- To fit on the left-hand side of DX³ and TX³ devices. Use the extension handle for association with 2 poles, 3 poles, 3 poles + neutral or 4 poles devices.

The product's benefits

Installation

- No tool required for joining together the motorised control and the main device

Usage

- Can take one control auxiliary and one signalling auxiliary.

Documentation

TECHNICAL DOCUMENTATION

 F01285FR-02.pdf | PDF (0.76Mo)

 F01285EN-02.pdf | PDF (0.84Mo)

 N0264H.pdf | PDF (2.53Mo)

CAD & Design specs / BIM

 406291.dwg | DWG (0.11Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0074.pdf | PDF (0.07Mo)