

Product sheet



SOLIROC™ LEGRAND

Soliroc™ - Socket RJ45 category 6A STP IK10 IP20

REF. 077899 | EAN. 3414970995575

> [Visit e-catalogue](#)

Product characteristics

- Category 6A STP : Data rate up to 10 GigaBit/s. This allows you to download a 1 GigaBytes file in 1 second. Shielded socket. Body and spreader made of metal alloy with copper/nickel coating.
- Protected against solid objects greater than 12,5mm (IP20)
- Protected against mechanical impacts up to 20 joules (IK10)
- 2 modules
- Mechanism delivered with frame

Recommendation / Restriction

- Suitable for public buildings, unsupervised passageways, car parks, communal areas in buildings.


Documentation


TECHNICAL DOCUMENTATION


 F03323FR-00.pdf | PDF (0.8Mo)

 F03323EN-00.pdf | PDF (0.8Mo)


Agreements & Certificates


 AoC-PL2_Cat6A_FFTP_32799_ac1171009 | (0.07Mo)


 AoC-CL4_Cat6A_STP_32869_ac1181045 | (0.08Mo)

 AoC-PL2_Cat6A_FTP_32778_ac1171014 | (0.08Mo)

 AoC-4PPoE 2019-676 Ac Delta Force | (0.08Mo)

 AoC-PL2_Cat6A_STP_32777_ac1171017A | (0.08Mo)

 AoC-CL2_Cat6A_STP_32777_ac1171018A | (0.08Mo)

 AoC-CL2_C6A_UFTP_32884_ac1191059 | (0.06Mo)

 AoC-CL2_C6A_STP_32882_ac1191063 | (0.06Mo)

The product's benefits


Installation

- RJ45 connectors are equipped with a locking nut. They do not require a special tool and can be re-wired if a mistake is made.

Avantages

- Toolless connector with fast connection thanks to integrated crimping.
- Compatible with cords equipped with RJ11, RJ12 or RJ45 plugs.

CATALOGUE PAGE & OTHERS

 ex223001_0800.pdf | PDF (0.1Mo)

-  AoC-CL2_Cat6A_FFTP_32799_ac1171010 | (0.07Mo)
-  AoC-CL4_Cat6A_STP_32778_ac1181044 | (0.08Mo)
-  AoC-CL2_C6A_FFTP_32883_ac1191061 | (0.06Mo)
-  AoC-CL2_Cat6A_FTP_32778_ac1171015 | (0.08Mo)
-  AoC-PL3_Cat6A_FTP_32778_ac1171016 | (0.08Mo)
-  AoC-PL2_C6A_FFTP_32883_ac1191060 | (0.06Mo)
-  AoC-PL3_Cat6A_STP_32777_ac1171019A | (0.08Mo)
-  AoC-PL2_C6A_STP_32882_ac1191062 | (0.06Mo)
-  AoC-PL3_Cat6A_FFTP_32799_ac1171011 | (0.07Mo)
-  AoC-PL2_C6A_UFTP_32884_ac1191058 | (0.06Mo)