

Product sheet



MOSAIC™ LEGRAND

RJ45 socket for snap-on columns and mini-columns category 6 FTP 2 modules Mosaic aluminium

REF. 079492 | EAN. 3245060794927

> [Visit e-catalogue](#)

Product characteristics

- RJ45 Cat 6 : Data rate up to 1 GigaBit/s. This allows you to download a 1 GigaBytes file in 8 seconds.
- Support high capacity PoE applications. Power over Ethernet pass electric power along with data on twisted pair Ethernet cabling.
- Equipped with a transparent protective dust cover protecting the connector, and four lateral fastening clips.
- 2 modules
- Aluminium

Recommendation / Restriction

- Strongly recommended if you consider to clip the socket onto snap-on columns or mini-columns to put the label space horizontally. Indoor use only. Conform to standards ISO/IEC 11801 Ed. 3.0, EN 50173-1 and TIA/EIA 568 C.

The product's benefits

Installation

- Supplied with rocker plates, to be equipped with support frames and plates. Equipped with connectors with quick toolless connection.

Usage

- The disposition of the fastening clips is specially designed for snap-on columns or mini-columns and let you place the label space horizontally. Suitable for commercial and residential installation. IP and analog phones. Very suitable for downloads, streaming or online games requiring low latency.

Advantages

- Toolless connector with fast connection thanks to integrated crimping.
- Compatible with cords equipped with RJ11, RJ12 or RJ45 plugs.
- Slot system allows a perfect and easy multigang setting. The support frames can be perfectly joined thereby easing the installation. Can be installed in a normal (single) flush mounting box, no need to additional wall groove cutting or cabling.

Documentation

TECHNICAL DOCUMENTATION

 F00949FR-08.pdf | PDF (0.78Mo)

→ LE01557AJ.pdf | PDF (1.55Mo)

CATALOGUE PAGE & OTHERS


 ex223001_1189.pdf | PDF (0.11Mo)


 ex223001_0986.pdf | PDF (0.11Mo)

 F00949EN-08.pdf | PDF (0.78Mo)

Agreements & Certificates


 LGRP-00945-V02.01-FR.pdf | PDF (0.8Mo)


 AoC-Ac Delta Force 4PPoE 2019-677 | (0.08Mo)

 AoC-PL3_Cat6_FTP_32756_ac1181022 | (0.07Mo)

 LGRP-00945-V02.01-EN.pdf | PDF (0.8Mo)

 AoC-PL2_Cat6FTP3275632856ac1181020 | (0.07Mo)

 AoC-SA52_SB52_ac109588 | (0.06Mo)

 AoC-CL2_Cat6FTP3275632856ac1181021 | (0.07Mo)