

Product sheet



PLEXO™ LEGRAND

Socket RJ45 Plexo IP66 IK08 category 6 FTP

REF. 090467 | EAN. 3245060904678

> [Visit e-catalogue](#)

Product characteristics

- Category 6 FTP : Data rate up to 1 GigaBit/s. This allows you to download a 1 GigaBytes file in 8 seconds.
- Weatherproof IP66
- Backbox screwed onto the support using 2 screws (diameter 4 to 4.5mm)
- Inclined 90°
- Light grey

Recommendation / Restriction

- For use in commercial and semi-industrial environments : high-pressure cleaning or with foam gun (food processing industry) less than 90 bars and less than 80°, fish auctions, ports, garages. Conforming to standards: ISO/IEC 11801 Ed2 and Amd, CENELEC EN 50173-1 2007, ANSI/EIA/TIA 568-C.2, IEC 60603-7 series

The product's benefits

Installation


- RJ45 connectors are equipped with a locking nut. They do not require a special tool and can be re-wired if a mistake is made.

Advantages


- Toolless connector with fast connection thanks to integrated crimping.
- Compatible with cords equipped with RJ11, RJ12 or RJ45 plugs.

Documentation

TECHNICAL DOCUMENTATION


 S000100762FR-03.pdf | PDF (0.88Mo)

→ LE01557AJ.pdf | PDF (1.55Mo)


 S000100762EN-03.pdf | PDF (0.91Mo)

Agreements & Certificates

 AoC-Ac Delta Force 4PPoE 2019-677 | (0.08Mo)

 AoC-PL2_Cat6FTP3275632856ac1181020 | (0.07Mo)

 AoC-SA52_SB52_ac109588 | (0.06Mo)

 AoC-CL2_Cat6FTP3275632856ac1181021 | (0.07Mo)

 AoC-PL3_Cat6_FTP_32756_ac1181022 | (0.07Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0987.pdf | PDF (0.09Mo)

 ex223001_0797.pdf | PDF (0.12Mo)