

Product sheet



LEGRAND

Line tap - non-shear - with feet - capacity per tap 2x50 mm² - hexagonal head

REF. 034044 | EAN. 3245060340445

[> Visit e-catalogue](#)

Product characteristics

- Line taps and equipotential bonding connectors Line taps non-shear line taps - Hexagonal head - With feet - Capacity per tap : 2 x 50 mm² - Width of slot : 9.5 max. cable Ø in mm - Overall height : 59 mm - Fixing centres : 44 mm

Documentation

TECHNICAL DOCUMENTATION

 F00003-01fr.pdf | PDF (0.04Mo)

 F00003-01en.pdf | PDF (0.04Mo)

 0064U92-01.pdf | PDF (0.01Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0820.pdf | PDF (0.22Mo)