

Product sheet



SYNERGY™ LEGRAND

Sinergy Sleek Double USB charger type A Brushed Stainless steel

REF. 832044 | EAN. 3414970660749

> [Visit e-catalogue](#)

Product characteristics

- 5Vdc, 2400mA, 12W
- Consumption in passive mode 0,1 W, overvoltages protected
- Battery picto to indicate for charging only
- Screwless cover plate is square 86x86 mm, product thickness is 4mm (once is installed onto the wall).
- Complete product, cover plates are clipped onto the mechanism itself.

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- 2P+E tap-off connection via 2.5 mm² screw terminals

Usage

- One gang to charge two portable devices such as smartphones, tablets, MP4 players, loudspeakers, watches, games consoles, power banks, ...

Advantages

- Plate in austenitic stainless steel Non magnetic Grade 304L
- USB 12W ideal for optimal charging of smartphones or tablets
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

Documentation

TECHNICAL DOCUMENTATION



F02315EN-00.pdf | PDF (0.62Mo)

CATALOGUE PAGE & OTHERS



ex223001_0729.pdf | PDF (0.1Mo)