

# Product sheet



## LEGRAND

Arteor™ - RJ45 socket category 5e UTP 1 module White

REF. 572303 | EAN. 3245065723038

> [Visit e-catalogue](#)

## Product characteristics

- RJ45 Cat 5e : Data rate up to 1 GigaBit/s. This allows you to download a 1 GigaBytes file in 8 seconds.
- Support high capacity PoE applications. Power over Ethernet pass electric power along with data on twisted pair Ethernet cabling.
- Equipped with a transparent protective dust cover protecting the connector.
- 1 module
- White

## Recommendation / Restriction

- Conform to standards ISO/IEC 11801 Ed. 3.0, EN 50173-1 and TIA/EIA 568 C. Indoor use only.

## The product's benefits

### Installation

- Supplied with rocker plates, to be equipped with support frames and plates. Equipped with connectors with quick toolless connection.

### Usage

- Suitable for commercial and residential installation. IP and analog phones. Very suitable for downloads, streaming or online games requiring low latency.

### Avantages

- Toolless connector with fast connection thanks to integrated crimping.
- Compatible with cords equipped with RJ11, RJ12 or RJ45 plugs.
- Slot system allows a perfect and easy multigang setting. The support frames can be perfectly joined thereby easing the installation. Can be installed in a normal (single) flush mounting box, no need to additional wall groove cutting or cabling.


## Documentation

### TECHNICAL DOCUMENTATION

 F00970EN-06.pdf | PDF (1.47Mo)

 LE02894AJ.pdf | PDF (2.05Mo)

### Agreements & Certificates

 AoC-PL2\_C5e\_UTP\_32751\_ac1181027 (H | (0.07Mo)

### CATALOGUE PAGE & OTHERS

 ex223001\_0992.pdf | PDF (0.08Mo)

 ex223001\_0581.pdf | PDF (0.07Mo)



LGRP-01108-V02.01-EN.pdf | PDF (0.83Mo)



AoC-SA01\_SB01\_ac109590 | (0.06Mo)



AoC-CL2\_C5e\_UTP\_32751\_ac1181028 | (0.07Mo)