

Product sheet



LEGRAND

Arteor™ - RJ45 socket category 6 STP 2 modules - Magnesium

REF. 572817 | EAN. 3245065728170

> [Visit e-catalogue](#)

Product characteristics

- RJ45 Cat 6 : Data rate up to 1 GigaBit/s. This allows you to download a 1 GigaBytes file in 8 seconds.
- Support high capacity PoE applications. Power over Ethernet pass electric power along with data on twisted pair Ethernet cabling.
- Equipped with a transparent protective dust cover protecting the connector.
- 2 modules
- Magnesium

Recommendation / Restriction

- Conform to standards ISO/IEC 11801 Ed. 3.0, EN 50173-1 and TIA/EIA 568 C. Indoor use only.

The product's benefits

Installation

- Supplied with rocker plates, to be equipped with support frames and plates. Equipped with connectors with quick toolless connection.

Usage

- Suitable for commercial and residential installation. IP and analog phones. Very suitable for downloads, streaming or online games requiring low latency.

Advantages

- Toolless connector with fast connection thanks to integrated crimping.
- Compatible with cords equipped with RJ11, RJ12 or RJ45 plugs.
- Slot system allows a perfect and easy multigang setting. The support frames can be perfectly joined thereby easing the installation. Can be installed in a normal (single) flush mounting box, no need to additional wall groove cutting or cabling.

Documentation

TECHNICAL DOCUMENTATION

 F00973EN-07.pdf | PDF (1.47Mo)

 LE02894AJ.pdf | PDF (2.05Mo)




 F00973FR-07.pdf | PDF (0.82Mo)

Agreements & Certificates

CATALOGUE PAGE & OTHERS

 ex223001_0580.pdf | PDF (0.12Mo)

 ex223001_0987.pdf | PDF (0.09Mo)

-  AoC-Ac Delta Force 4PPoE 2019-677 | (0.08Mo)
-  AoC-PL2_C6_STP_32757_ac1181031 | (0.08Mo)
-  AoC-CL2_C6_STP_32757_ac1181032 | (0.08Mo)