

Product sheet



HYPRA LEGRAND

Panel mounting socket Prisinter Hypra - IP 44 - 380/415 V~ -16 A - 3P+E -plastic

REF. 052203 | EAN. 3245060522032

> [Visit e-catalogue](#)

Product characteristics

- Hypra IP 44 sockets and plugs metal, plastic, rubber, IP 44/55 Prisinter - LV 16 to 63 A and ELV 16 and 32 A - Conform to IEC 60309 - 1 and IEC 60309 - 2 - IP 44 according to IEC 60529 - IK 09 : plastic and rubber - IK 10 : metal according to IEC 62262 - Self - extinguishing : - 850°C (support of active parts) / 960 °C for Prisinter) - 650 °C : plastic housing conform to IEC 60695 - 2 - 10 - 50°C to + 100°C (- 20°C for Prisinter) LV prisinters - Dust resistance IP may be increased by rubber push - button (on request) - IP 55 cover closed or connected - IP 44 connected 380 to 415 V~ 50/60 Hz - 16 A 3P+E - To be associated with surface - mounting box Cat. No 0 520 49 for surface - mounting socket - Panel mounting socket - plastic - 16 A

Documentation

TECHNICAL DOCUMENTATION

-  F00097FR-05.pdf | PDF (0.88Mo)
-  F00097EN-05.pdf | PDF (0.99Mo)

CAD & Design specs / BIM

- LEGRAND_INTERLOCKED_SOCKETS_FLUSH_MOUNTED_400.rfa | RFA (0.61Mo)
- LEGRAND_PRISES_VERROUILLEES_ENCASTREES_400.rfa | RFA (0.61Mo)
-  052203.dwg | DWG (0.18Mo)

Agreements & Certificates

-  OC / CB-FR_710635/A1 | (0.72Mo)