

Product sheet



LEGRAND

Cam switch - ammeter - PR 12 - 16 A - 9 contacts - 3 independent CT - screw fixing

REF. 027535 | EAN. 3245060275358

> [Visit e-catalogue](#)

Product characteristics

- Cam switches screw Fixing on door - For selecting and changing the status of the circuits into which it is integrated - For viewing the state of equipment according to the position of the selector lever - Mounting on enclosure doors - Contacts with positive opening and double breaking of poles - Presentation : grey/black selector lever - aluminium faceplate with marking - Conform to standards IEC EN 60947 - 3 - Approved to UL - CSA (USA - Canada) - IP 40 at front of enclosure (selector lever) - IP 2X at back of enclosure up to PR 26
- Function : selective measurement switches Ammeters - Range : PR 12 - Max. rating AC 21 : 16 A - Number of contacts : 9 - Function : 3 C.T. with common point without C.T. 3 independent C.T.

Documentation

TECHNICAL DOCUMENTATION

→ 096897001-01.pdf | PDF (0.72Mo)

Agreements & Certificates

 UL recogn-280206-E57817 | (0.18Mo)

 OC / CB-FR 60026094B | (0.32Mo)

 CSA-1725160 | (0.1Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0493.pdf | PDF (0.37Mo)