

Product sheet



MOSAIC™ LEGRAND

Proximity MCB Mosaic - single pole - with neutral 230 V~ - 16 A - 2 mod - white

REF. 077522 | EAN. 3245060775223

> [Visit e-catalogue](#)

Product characteristics

- Mosaic™ Programme mechanisms - voltage surge protector, replacement module, filter, buzzers, bells, blanking plates, cable outlets and proximity MCBs
- Proximity MCBs - Used for local protection of part of a circuit against overloads and short circuits - Used in addition to the main protection device - Due to its proximity to the user and its discrimination with the main protection device, the restart can be immediate - 2 modules Single pole thermal magnetic MCB + Neutral 230 V~ - Can also be used as a local consumption limiter (depending on its rating) - Breaking capacity : 3000 A - NF C 61 - 410 (10/16 A) 1500 A - NF C 61 - 410 (6 A) - White - 16 A

Documentation

CATALOGUE PAGE & OTHERS

 ex223001_1187.pdf | PDF (0.21Mo)

Agreements & Certificates

 OC / CB-8320-M1 | (0.08Mo)

 IMQ-CA03.00605 | (0.25Mo)

CAD & Design specs / BIM

BIM-LEGRAND-MOSAIC-2023-ENGLISH.rvt | RVT (126.68Mo)

BIM-LEGRAND-MOSAIC-2023-FRANCAIS.rvt | RVT (128.48Mo)