

Product sheet



LCS² LEGRAND

LCS² - Keystone RJ 45 socket category 6 UTP fast crimping connection

REF. 033181 | EAN. 3245060331818

RJ45 connector equipped with a rotating locking system. Suitable for category 6 U/UTP AWG 22 single-core cables up to AWG 26 and AWG multicore cables. It enables high speed data transmission.

> [Visit e-catalogue](#)

Description

RJ45 connector equipped with a rotating locking system. Suitable for category 6 U/UTP AWG 22 single-core cables up to AWG 26 and AWG multicore cables. It enables high speed data transmission.

Product characteristics

- Category 6 UTP : Data rate up to 1 GigaBit/s. This allows you to download a 1 GigaBytes file in 8 seconds. Unshielded cable
- With fast crimping connection
- Accepts the following cable connectors : RJ11 (4 contacts), RJ12 (6 contacts), RJ45 (9 contacts).

Recommendation / Restriction

- Max. number of connections and disconnections: 5 without refreshing the cable. Conform to standards ISO/IEC 11801 Ed. 3.0, EN 50173-1 and TIA/EIA 568 C

Documentation

TECHNICAL DOCUMENTATION

→ LE02966AG.pdf | PDF (0.94Mo)

F01418EN-04.pdf | PDF (0.78Mo)

Agreements & Certificates

AoC-PL2_C6_UTP_32886_ac1191056 | (0.06Mo)

AoC-PL3_Cat6_UTP_32754_ac1181026 | (0.07Mo)

AoC-Ac Delta Force 4PPoE 2019-677 | (0.08Mo)

AoC-SA51_SB51_ac109587 | (0.06Mo)

LGRP-01127-V02.01-EN.pdf | PDF (0.79Mo)

AoC-CL2_C6_UTP_32886_ac1191057 | (0.06Mo)

The product's benefits

Installation

- The RJ45 connectors are equipped with a rotating locking system that does not require special tools and enables rewiring in the event of error. Can be integrated in several supports : Axolute, Living Light, Light Tech, Matix.

Usage

- High reliability : 2500 movements (plug insertion/withdrawal)

CATALOGUE PAGE & OTHERS

ex223001_0987.pdf | PDF (0.09Mo)

-  AoC-CL2_Cat6UTP3275432861ac1181025 | (0.07Mo)
-  AoC-CL4_Cat6_UTP_32866_ac1181047 | (0.08Mo)
-  AoC-CL4_Cat6_UTP_32754_ac1181046 (| (0.08Mo)
-  AoC-PL2_Cat6_UTP_32754_ac1181024 | (0.07Mo)