

# Product sheet



LEGRAND

Rigid conduit - with coupling - shock resistance 2 joules -  $\varnothing$  ext. 16 mm

REF. 651416 | EAN. 3245066514161

[> Visit e-catalogue](#)

## Product characteristics

- Rigid conduits Medium impact rigid conduits with integrated coupling - PVC without Pb, Sn, Cd (RoHS compliant) - Non flame propagating - Surface - mounting or flush-mounting - Suitable for prefabricated concrete - Conforming to European standard : EN/IEC 61386 - 21 - Crush resistance : 750 Newtons - Impact resistance : 2 joules at - 5 °C - Min operating t° : - 5 °C. Max operating t° : + 60 °C. IK 07 - Can be used outside - Supplied wrapped in film. Light grey (RAL 7035). Length of tubes : 3 m -  $\varnothing$  exterior : 16 mm -  $\varnothing$  interior : 13 mm - thickness : 1.50 mm

## Documentation

### TECHNICAL DOCUMENTATION

 F01719EN-02.pdf | PDF (0.17Mo)

### CATALOGUE PAGE & OTHERS

 ex223001\_0814.pdf | PDF (0.35Mo)

 ex223001\_0815.pdf | PDF (0.12Mo)