

Product sheet



SPD LEGRAND

Surge protective device for PV instalation 1000V Type 2- I_{max} 40kA

REF. 414156 | EAN. 3414970806895

> [Visit e-catalogue](#)

Product charateristics

- Maximum operating voltage U_{cpv} = 1200V DC, rated current I_n = 20kA
- Permissible current of the surge arrester without additional external protection : I_{scwpv} = 125A.

The product's benefits

Installation

- Connectors at the top. No connection direction for the +/- terminals, which can be wired indifferently on the left or right module to facilitate installation. Replacement plug-in modules equipped with retractable gripper for easy extraction and replacement.

Usage

- Consisting of detachable and interchangeable plug-in for easy maintenance. The status of the surge arrester can be visualized by the warning light on the front face or remotely by the integrated remote status report function.

Documentation

TECHNICAL DOCUMENTATION

-  F01271FR-02.pdf | PDF (1.18Mo)
-  F01271EN-02.pdf | PDF (1.18Mo)
-  LE09132AB_01.pdf | PDF (0.79Mo)

CAD & Design specs / BIM

-  414155.dwg | DWG (0.11Mo)

CATALOGUE PAGE & OTHERS

-  ex223001_0090.pdf | PDF (0.05Mo)