

Product sheet



MOSAIC™ LEGRAND

Metal back box for installation of floor boxes and ducts

REF. 089634 | EAN. 3245060896348

> [Visit e-catalogue](#)

Product characteristics

- Height adjustable (its height must be equal to the height of the screed) using 4 screws located in the box corners and a tool adapting to electric drill or screwdriver
- For coating thickness (tile, marble) between 6 and 28 mm
- Back boxes made in galvanised steel (Z275) and Zamak
- Delivered with worksite protection cover to be replaced by adaptor Ref. 0 896 83 or 0 896 84

Recommendation / Restriction

- For installation in concrete floor only - Temperature of use, transport and storage: -5° à +60°

The product's benefits

Installation



- Bendable side walls for junction with different sizes of floor ducts

Advantages

- Allows the derivation of strong or low currents and / or the installation of floor boxes: - reduced height 65 mm - adjustable height from 65 to 105mm

Documentation

TECHNICAL DOCUMENTATION

-  F00638FR-01.pdf | PDF (0.3Mo)
-  F00638EN-01.pdf | PDF (0.26Mo)
-  F00838FR-06.pdf | PDF (1.08Mo)
-  LE01852AA.pdf | PDF (2.27Mo)
-  F00838EN-06.pdf | PDF (1.05Mo)
-  F00839EN-05.pdf | PDF (0.89Mo)
-  F00839FR-05.pdf | PDF (0.93Mo)

CAD & Design specs / BIM

- Legrand-boites-de-sol-charge-lourde-FR.rfa | RFA (1Mo)
- Legrand-heavy-duty-floor-boxes-EN.rfa | RFA (1Mo)

CATALOGUE PAGE & OTHERS

-  ex223001_1164.pdf | PDF (0.11Mo)