

Product sheet



DLP-S LEGRAND

Internal angle for DLP-S mini-trunking 15x10mm

REF. 638101 | EAN. 3245066381015

> [Visit e-catalogue](#)

Product characteristics

- Internal angle 90 degrees
- Respect the protection index
- Improvement of aesthetics (covering of the cut)
- Colour: white

The product's benefits

Installation

- Clips directly on the body of the mini-trunking

Usage

- Allows a neat and clean electrical installation finish

Advantages

- Important saving-time on implementation by avoiding 45-degree cuts

Documentation

TECHNICAL DOCUMENTATION

 F01197EN-07.pdf | PDF (2.05Mo)

 F01197FR-05.pdf | PDF (2.05Mo)

CAD & Design specs / BIM

 LG-638101.stp | IFC (0.06Mo)

CATALOGUE PAGE & OTHERS

 ex223001_1051.pdf | PDF (0.09Mo)

 ex223001_1053.pdf | PDF (0.06Mo)

Agreements & Certificates

 LGRP-01518-V01.01-EN.pdf | PDF (0.62Mo)