

Product sheet



LEGRAND

Cam switch - changeover switch with off - PR 40 - 3P - 50 A - box 135x170 mm

REF. 027747 | EAN. 3245060277475

> [Visit e-catalogue](#)

Product characteristics

- Cam switches insulating box - For selecting and changing the status of the circuits into which it is integrated - For viewing the state of equipment according to the position of the selector lever - Boxed device, class II - Contacts with positive opening and double breaking of poles - Presentation : black or grey/black selector lever, faceplate with marking - Conform to standards IEC EN 60947 - 3 - IP 65 for 76 x 76 and 96 x 120 mm boxes - IP 55 for 135 x 170 mm boxes
- Function : changeover switch With off - 135 x 170 mm box - Number of poles : 3 - Range : PR 40 - Max. rating AC 21 : 50 A - Number of contacts : 2

Documentation

TECHNICAL DOCUMENTATION

→ 096897001-01.pdf | PDF (0.72Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0490.pdf | PDF (0.08Mo)

 ex223001_0492-0493.pdf | PDF (0.37Mo)

 ex223001_0491.pdf | PDF (0.04Mo)

Agreements & Certificates

 UL recogn-280206-E57817 | (0.18Mo)

 OC / CB-FR60026094C | (0.32Mo)

 CSA-1725160 | (0.1Mo)