

# Product sheet



MOSAIC™ LEGRAND

Single TV male socket Mosaic - star 1.5 dB - 1 module - white

REF. 078793 | EAN. 3414970328700

> [Visit e-catalogue](#)

## Product characteristics

- Mosaic™ Programm e mechanisms - television sockets - For DVBT, Cablecast and satellite installation - UHD TV compatible - Class A shielded star sockets LTE Ready (4G protected) Recomm ended coaxial cable : 17 VATC - Star cabling (1 socket = 1 cable to antenna, splitter or multiswitch) Visual checking of the connection - Meet EN 50083 - 4 and EN 50083 - 2 European directive - TV : male connector (Ø9.5 mm ) - 5 - 68 / 120 - 862 MHz - R : female connector (Ø9.5 mm ) - 87.5 - 108 MHz - SAT : "F type" connector - 950 - 2400 MHz
- Single TV star sockets - Low attenuation : 1 dB TV 9.5 mm male - White - 1 module

## Documentation

### TECHNICAL DOCUMENTATION

-  S000090598EN-02.pdf | PDF (0.33Mo)
-  LE08364AA.pdf | PDF (1.12Mo)
-  S000090598FR-02.pdf | PDF (0.33Mo)

### CAD & Design specs / BIM

- BIM-LEGRAND-MOSAIC-2023-ENGLISH.rvt | RVT (126.68Mo)
- BIM-LEGRAND-MOSAIC-2023-FRANCAIS.rvt | RVT (128.48Mo)

### CATALOGUE PAGE & OTHERS

-  ex223001\_0877.pdf | PDF (0.08Mo)
-  ex223001\_1191.pdf | PDF (0.1Mo)