

Product sheet



NYLBLOC™ LEGRAND

Screwless connection terminal Nylbloc auto - for 8 wires - 24 A - 450 V~

REF. 034328 | EAN. 3245060343286

> [Visit e-catalogue](#)

Product characteristics

- Nylbloc™ auto - screwless connection terminals Screwless connection terminals - Nylbloc auto - No tool direct connection after simple stripping of copper conductors - Test socket for tester screwdriver or test tip Cat.No 0 394 45 for IP 2X test or Ø4 mm tip on Nylbloc auto terminals - Conform to EN 60998 - 2 - 2 - For rigid cable from 0,75 to 2.5 mm² - Stripping length : 11 mm - Connection by separate crimping blades - Transparent base providing full visibility of the connections - Colour code to identify products - Duplix marking possible on 3, 5 and 8 - wire terminals - Max. intensity : 24 A. Insulating voltage : 450 V~ - Grey terminal for 8 wires

Documentation

TECHNICAL DOCUMENTATION

→ 041275-01.pdf | PDF (0.15Mo)

Agreements & Certificates

 AENOR-030/002395 | (0.32Mo)

 NF App Domestic-650685A | (0.13Mo)

 IMQ-CA02.01935 | (0.66Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0819.pdf | PDF (0.1Mo)