

Product sheet



LEGRAND

Cable glands metal - IP68 - PG 29 - clamping capacity 16-26 mm

REF. 095516 | EAN. 3245060955168

> [Visit e-catalogue](#)

Product characteristics

- Metal cable glands IP 68 - ISO and PG
- Metal cable glands - Mechanically tightened cable glands with neoprene weatherproof seal for IP 68 protection. - Locking part consisting of flexible blades which exert strong pressure on the cable thus giving the product excellent tensile strength - Supplied with surface seal mounted PG - Conform to UTE C 68 - 300 and 68 - 312 guides recommendations - PG : 29 - Clamping capacity Min. : 16 mm - Clamping capacity Max. : 26 mm

Documentation

TECHNICAL DOCUMENTATION

 F02550FR00.pdf | PDF (2.13Mo)

CAD & Design specs / BIM

 095516.dwg | DWG (0.06Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0445.pdf | PDF (0.06Mo)

Agreements & Certificates

 LGRP-2014-115-V1-EN.pdf | PDF (0.96Mo)