

Product sheet



LEGRAND

Cable glands metal - IP 68 - ISO 40 - Clamping capacity diameter 15-27 mm

REF. 095507 | EAN. 3245060955076

[> Visit e-catalogue](#)

Product characteristics

- Metal cable glands IP 68 - ISO and PG
- Metal cable glands - Mechanically tightened cable glands with neoprene weatherproof seal for IP 68 protection. - Locking part consisting of flexible blades which exert strong pressure on the cable thus giving the product excellent tensile strength - Supplied with surface seal mounted ISO - Conform to EN 50262 - ISO : 40 - Clamping capacity Min. : 15 mm - Clamping capacity Max. : 27 mm

Documentation

TECHNICAL DOCUMENTATION



F02550FR00.pdf | PDF (2.13Mo)

CAD & Design specs / BIM



095507.dwg | DWG (0.06Mo)

CATALOGUE PAGE & OTHERS



ex223001_0445.pdf | PDF (0.06Mo)

Agreements & Certificates



LGRP-2014-115-V1-EN.pdf | PDF (0.96Mo)