

# Product sheet



PLEXO™ LEGRAND

Round Plexo box with 4 direct entry membrane glands  
- IP55 IK07 - Ø60 height 40 - grey RAL 7035

REF. 092001 | EAN. 3245060920012

[> Visit e-catalogue](#)

## Product characteristics

- Plexo boxes IP 55 - IK 07 - with direct entry membrane glands - 650°C - IP 55 - IK 07 - Resistance to incandescent wire 650°C - For use as junction boxes in any type of normal installation circuit - Operating temperature : - 25 to +40°C - Interchangeable membrane glands with direct entries for IRL tubes up to 16 and R02V cables, with marked cut - out for IRL tube greater than 16 - Captive cover with tie. Space for marking on both sides of the cover. Fixing with vertical level adjustment. Class II is ensured by protective caps (supplied) for the Fixing screws - boxes without halogenated flame retardants (European Directive RoHS 2002/95/EC)
- Round boxes - Clippable covers - 4 membrane glands - Accepted cable and tube : 4 to 20 mm - Grey RAL 7035 - 60 - height 40

## Documentation

### TECHNICAL DOCUMENTATION

 F01039EN-03.pdf | PDF (1.16Mo)

 F01039FR-03.pdf | PDF (1.19Mo)

### CAD & Design specs / BIM

 3D\_LG-092001.stp | IFC (0.87Mo)

### CATALOGUE PAGE & OTHERS

 ex223001\_0801.pdf | PDF (0.1Mo)

### Agreements & Certificates

 LGRP-01610-V02.01-FR.pdf | PDF (0.76Mo)

 OC / CB-FR\_715099 | (0.51Mo)