

# Product sheet



PLEXO™ LEGRAND

Box Plexo - IP 55 - IK 07 - 180x140x86 - knock-out ISO cable entries

REF. 092054 | EAN. 3245060920548

[> Visit e-catalogue](#)

## Product characteristics

- Plexo™ boxes IP 55 - IK 07 - with pre - cut knock - out ISO type cable entries - Resistance to glow wire test : 750 °C (EN 60695 2 - 11) - Operating temperature : - 25 °C to + 40 °C - Knock - out entries - Captive cover with clippable tie between box and cover except boxes 310 x 240 and 360 x 270 - Cover opens/closes with a 1/4 turn of a regular screwdriver, marking 0 and I - Fixing with level adjustment - At 2 or 4 internal points (screw Ø5 mm max.) - At the four corners out of wiring volume (screw Ø4 mm max.) - With brackets Cat.No 0 358 02 - Class II is ensured by protection caps (supplied) for the attachment screws Rectangular boxes - Grey RAL 7035180 x 140 x 86 mm - 16 knock - out entries for ISO 16/20 - 4 knock - out entries for ISO 20/25

## Documentation

### TECHNICAL DOCUMENTATION

 [fa343afr.pdf](#) | PDF (0.03Mo)

### CATALOGUE PAGE & OTHERS

 [ex223001\\_0803.pdf](#) | PDF (0.15Mo)

 [ex223001\\_0804-0805.pdf](#) | PDF (0.32Mo)