

Product sheet



SYNERGY™ LEGRAND

Synergy™ Sleek - TV-R-SAT socket - Brushed Stainless Steel

REF. 832043 | EAN. 3414970660725

> [Visit e-catalogue](#)

Product characteristics

- TV : male diameter 9,5mm, R : female connector diameter 9,5mm, SAT : F type connector
- Low attenuation 1dB max
- Screwless cover plate is square 86x86 mm, product thickness is 4mm (once is installed onto the wall).
- Complete product, cover plates are clipped onto the mechanism itself.

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- This TV socket has been designed for intuitive cable insertion. Connection to the terminal block is quick and easy. To allow easier delivery into the box, the terminal block has been placed in the center of the mechanism. Finally the visualization of the connection allows to know with certainty if the cable is well tightened

Usage

- Optimized socket for new UHD or 4K TVs: designed for optimal signal reception

Advantages

- Plate in austenitic stainless steel Non magnetic Grade 304L
- Class A certified shield: protects from interference caused by new signals used by mobile phones (3G, 4G, 5G). These unwanted signals can cause pixelation, image jamming and sound disturbances. Legrand uses the PKM laboratory for the certification of its class A TV sockets.
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

Documentation

CATALOGUE PAGE & OTHERS

 ex223001_0730.pdf | PDF (0.09Mo)

