

# Product sheet



SYNERGY™ LEGRAND

Synergy Authentic Cable outlet 20A - Brushed Stainless steel

REF. 833019 | EAN. 3414970664600

> [Visit e-catalogue](#)

## Product characteristics

- 20A 250V~
- Screw type terminals for enhanced contacts
- Marked terminals for easy identification
- Cover plate is square 86x86 mm, product thickness is 7mm (once is installed onto the wall).
- Monobloc complete product = ready-to-install product

## Recommendation / Restriction

- Recommended inside use only

## The product's benefits

### Installation

- Terminal screws backed off ready to cabling

### Usage

- Aesthetic solution for devices requesting hard-wiring connection

### Advantages

- Plate in austenitic stainless steel Non magnetic Grade 304L
- Made in UK
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

## Documentation

### TECHNICAL DOCUMENTATION



F02358EN-00.pdf | PDF (0.1Mo)



ex223001\_0726.pdf | PDF (0.1Mo)