

Product sheet



LEGRAND

MCCB - DRX 125 - thermal magnetic - Icu 20 kA - 415 V~ - 4P - In 20 A

REF. 027031 | EAN. 3245060270315

> [Visit e-catalogue](#)

Product characteristics

- DRX 125 - thermal magnetic MCCBs from 15 to 125 A - For switching, control, isolation and protection of low - voltage electrical lines - Can be fitted with auxiliaries - Supplied with : - M5 terminal for In ≤ 50 A and M8 range for In 50 A - Fixing screws - Insulating shields (2 for 3P and 3 for 4P) - Fixed thermal and magnetic - Conform to IEC 60947 - 2, in compliance with NEMA
- DRX 125 Breaking capacity Icu 20 kA (415 V~) - 4P - 20 A

Documentation

TECHNICAL DOCUMENTATION

 F00699EN06_DRX125.pdf | PDF (0.96Mo)

→ Y1036G.pdf | PDF (0.58Mo)

CAD & Design specs / BIM

 027010.dwg | DWG (0.23Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0132.pdf | PDF (0.13Mo)

 ex223001_0136.pdf | PDF (0.07Mo)

 ex223001_0138.pdf | PDF (0.05Mo)

Agreements & Certificates

 LGRP-01099-V01.01-EN.pdf | PDF (0.62Mo)

 OC / CB-SE-101774A1 | (0.42Mo)

 OC / CB-SE 57102 | (0.2Mo)