

Product sheet



LEGRAND

MCCB - DRX 250 - thermal magnetic - Icu 25 kA - 415 V~ - 4P - In 125 A

REF. 027118 | EAN. 3245060271183

[> Visit e-catalogue](#)

Product characteristics

- DRX 250 - thermal magnetic MCCBs from 125 to 250 A - For switching, control, isolation and protection of low - voltage electrical lines - Can be fitted with auxiliaries - Supplied with : - M8 terminals - Fixing screws - Insulating shields (2 for 3P and 3 for 4P) - Fixed thermal and magnetic - Conform to IEC 60947 - 2
- DRX 250 Breaking capacity Icu 25 kA (415 V~) - 4P - 125 A

Documentation

TECHNICAL DOCUMENTATION

- [→ Y1393D.pdf](#) | PDF (0.58Mo)
- [F00703EN05_DRX250.pdf](#) | PDF (0.95Mo)

CAD & Design specs / BIM

- [027106.dwg](#) | DWG (0.18Mo)

CATALOGUE PAGE & OTHERS

- [ex223001_0141.pdf](#) | PDF (0.04Mo)
- [ex223001_0139.pdf](#) | PDF (0.05Mo)
- [ex223001_0133.pdf](#) | PDF (0.16Mo)

Agreements & Certificates

- [OC / CB-SE 57105](#) | (0.2Mo)
- [OC / CB-SE-101271](#) | (0.08Mo)