

# Product sheet



## P 17 TEMPRA LEGRAND

Surface mounting socket P17 - IP66/67 - 200/250 V~ - 32 A - 2P+E

REF. 555454 | EAN. 3245065554540

[> Visit e-catalogue](#)

## Product characteristics




- P 17 Tempra Pro IP 66/67 LV 16 and 32 A Surface mounting sockets - Two possible angles (5° or 25°) 200/250 V~ - 32 A - 2P+E

## Documentation


### TECHNICAL DOCUMENTATION

-  F01811FR-02.pdf | PDF (3.67Mo)
-  LE05815AA-01.pdf | PDF (2.53Mo)
-  F01811EN-03.pdf | PDF (9.37Mo)




### CAD & Design specs / BIM

-  surface\_no\_interlocked\_sockets\_200\_250V.rfa | RFA (1.31Mo)
-  Prises\_non\_verrouillées\_saillies\_200\_250V.rfa | RFA (1.31Mo)
-  555454.dwg | DWG (0.13Mo)

### CATALOGUE PAGE & OTHERS

-  ex223001\_0527.pdf | PDF (0.11Mo)
-  ex223001\_0533.pdf | PDF (0.07Mo)
-  ex223001\_0534.pdf | PDF (0.06Mo)

### Agreements & Certificates

-  IMQ-CA02.05951 | (0.42Mo)
-  OC / CB-FR\_710665 | (0.7Mo)
-  LGRP-2014-112-V1-EN.pdf | PDF (1.02Mo)