

Product sheet



P 17 TEMPRA LEGRAND

Surface mounting socket P17 - IP66/67 - 200/250 V~ - 32 A - 3P+N+E

REF. 555456 | EAN. 3245065554564

> [Visit e-catalogue](#)

Product characteristics

- P 17 Tempra Pro IP 66/67 LV 16 and 32 A Surface mounting sockets - Two possible angles (5° or 25°) 200/250 V~ - 32 A - 3P+N+E

Recommendation / Restriction

- Not suitable for charging electric vehicles

Documentation

TECHNICAL DOCUMENTATION

 F01811FR-02.pdf | PDF (3.67Mo)

 F01811EN-03.pdf | PDF (9.37Mo)

 LE05815AA-01.pdf | PDF (2.53Mo)

CAD & Design specs / BIM

Prises_non_verrouillées_saillies_200_250V.rfa | RFA (1.31Mo)

 555456.dwg | DWG (0.13Mo)

surface_no_interlocked_sockets_200_250V.rfa | RFA (1.31Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0527.pdf | PDF (0.11Mo)

 ex223001_0533.pdf | PDF (0.07Mo)

 ex223001_0534.pdf | PDF (0.06Mo)

Agreements & Certificates

 OC / CB-FR_710665 | (0.7Mo)

 IMQ-CA02.05951 | (0.42Mo)

 LGRP-2014-112-V1-EN.pdf | PDF (1.02Mo)