

Product sheet



LEGRAND

Clipssable office multioutlet 4 outlets 2 USB ports
cable 1,5m

REF. 694812 | EAN. 3414971162020

> [Visit e-catalogue](#)

Product characteristics

- 4 german sockets 16A 230V 3680W
- 2 ports USB type A (1,5A & 2,4A)
- Illuminated switch commands sockets and USB ports
- ABS plastic body
- Black PVC rotating 90 ° cord 3x1,5mm² 1,5m

Recommendation / Restriction

- Indoor

The product's benefits

Installation

- Clipssable multioutlet that unclutters workspace at the office or at home. Clipssable arm that maintains the multioutlet to the table (32mm minimum and 63mm maximum)

Usage

- Fits all workspaces, at the office or at home. It may clipse anywhere or you can put on the desk

Avantages

- Neat finish with ergonomic design
- Glossy and matte finish
- PVC black cord 3x1,5mm²

Documentation

CATALOGUE PAGE & OTHERS

 [ex223001_0834.pdf](#) | PDF (0.12Mo)

Agreements & Certificates

 [MEEI-UP 69262122](#) | (0.14Mo)

 [OC / CB-FR_705481](#) | (0.51Mo)