

Product sheet



LEGRAND

MCCB DPX³ 630 - thermal magnetic - 3P+N/2 - Icu 36 kA (400 V~) - In 400 A

REF. 422011 | EAN. 3414970378071

> [Visit e-catalogue](#)

Documentation

TECHNICAL DOCUMENTATION

- LE07062AB.pdf | PDF (0.81Mo)
-  F01958FR01_DPX3_630MT_FRAv3.pdf | PDF (0.71Mo)
-  EXB15015_TG_Coordination_EN.pdf | PDF (5.41Mo)
-  EXB19026_CA_DPX3_125HP250HP_630_1600EN.pdf | PDF (82.93Mo)
-  F01958EN04_DPX3630_MT__ENG.pdf | PDF (1.85Mo)
-  EXB21086_CA_DPX3HP125_250_DPX3630_1600FR.pdf | PDF (83.49Mo)

CAD & Design specs / BIM

-  422009.dwg | DWG (0.18Mo)

CATALOGUE PAGE & OTHERS

-  ex223001_0176.pdf | PDF (0.08Mo)
-  ex223001_0194-0195.pdf | PDF (0.48Mo)
-  ex223001_0198.pdf | PDF (0.03Mo)

Agreements & Certificates

-  LGRP-00702-V01.01-EN.pdf | PDF (1.02Mo)
-  OC / CB-SE-91828 | (1.11Mo)