

Product sheet



LEGRAND

MCCB DPX³ 630 - S2 elec release + central - 4P - Icu 36 kA (400 V~) - In 630 A

REF. 422105 | EAN. 3414970379016

> [Visit e-catalogue](#)

Product characteristics

- DPX³ 630 - S2 electronic release MCCBs from 250 to 630 A - Moulded case MCCBs for switching, control isolation and protection of low voltage electrical lines - Can be fitted with auxiliaries - Can be used with earth leakage modules or with residual current relays - Supplied complete with : - Fixing screws - Connection plates for bars - Insulated shields (phase barriers) - Conform to IEC 60947 - 2 - Sealable adjustment - Can be mounted on plate in XL³ cabinets and enclosures
- MCCBs electronic release S2 with energy metering central unit - fixed version - Adjustment of Ir, Isd, tr, tsd - Instantaneous protection If = 5 kA - Green indicator lamp - Connector for test unit - Logic and dynamic selectivity - 4P version : adjustment of neutral on Front panel Breaking capacity Icu 36 kA (400 V~) - 4P - In : 630 A

Documentation

TECHNICAL DOCUMENTATION

- LE07062AB.pdf | PDF (0.81Mo)
- ModbusTable_18.pdf | PDF (0.41Mo)
- LE07061AA-02.pdf | PDF (1.99Mo)
- F01959EN03_DPX3630_ELE_ENG.pdf | PDF (3Mo)
- EXB15015_TG_Coordination_EN.pdf | PDF (5.41Mo)
- EXB21086_CA_DPX3HP125_250_DPX3630_1600FR.pdf | PDF (83.49Mo)
- F01959FR01_DPX3_630ELE_FRAv3.pdf | PDF (1.04Mo)
- EXB20072_logic_selectivity (print).pdf | PDF (6.63Mo)
- EXB19026_CA_DPX3_125HP250HP_630_1600EN.pdf | PDF (82.93Mo)
- PRT220015_GT_selectivite_logique.pdf | PDF (6.38Mo)

CAD & Design specs / BIM

- 422105.dwg | DWG (0.19Mo)

Software & configurators

- SW_Legrand_PowerControlStation.exe | EXE (32.62Mo)

CATALOGUE PAGE & OTHERS

- ex223001_0199.pdf | PDF (0.04Mo)

Agreements & Certificates

- DC-D13_13-SELECTIVITE _FILIAION-A-3-NIVEAUX.pdf | PDF (0.62Mo)

 PowerControlStation 5.0.70.exe | EXE (43.37Mo)