

# Product sheet



## LEGRAND

HRC cartridge fuse - cylindrical type aM 14 X 51 - 10 A - without indicator

REF. 014010 | EAN. 3245060140106

> [Visit e-catalogue](#)

## Product characteristics

- HRC cartridge fuses
- Cylindrical type aM (motor rated) - Conform to EN 60269 - 1, IEC 60269 - 1 and 214 x 51 HRC - Without striker - Rating : 10 Amps - Voltage ~ : 500 Volts - Rupture capacity : 100000 Amps

## Documentation

### TECHNICAL DOCUMENTATION

-  F00188EN-08.pdf | PDF (2.04Mo)
-  F00188FR-08.pdf | PDF (2.08Mo)

### CATALOGUE PAGE & OTHERS

-  ex223001\_0263.pdf | PDF (0.05Mo)
-  ex223001\_0264.pdf | PDF (0.05Mo)
-  ex223001\_0261.pdf | PDF (0.1Mo)