

Product sheet



XL³ S 630 LEGRAND

Distribution enclosure XL3 S 630 usable faceplate height 750 mm width 36 modules

REF. 337523 | EAN. 3414970898043

> [Visit e-catalogue](#)

Product characteristics

- Allows installation of MCCBs devices type DPX3 and DRX, SPX, modular devices, and other devices
- Used to create assemblies certified IEC 61439 - 2
- IP30 ensuring protection against solid bodies larger than 2,5 mm with IP30 finishing kit
- IP40 with door ensuring protection against solid bodies larger than 1 mm . IP43 with accessory 3 379 51
- Fixing accessories, lateral panels , angle and sides for plinths to be ordered separately

Recommendation / Restriction

- Internal use only

The product's benefits

Installation

- Joinable enclosures, very simple installation of fixing accessories, complete range for all sizes, full or perforated plates for all type of devices

Usage

- Can be equipped with a transparent or plain door reversible and different type of devices like blanking plates, clip on holders, document holders...

Avantages

- XL3 S 630 enclosures belong to the largest range of the market in this category

Documentation

TECHNICAL DOCUMENTATION

-  F02369EN-01.pdf | PDF (2.28Mo)
-  EXB22009_Flipbook_FR_(03_2022).pdf | PDF (6.2Mo)
-  EXB22010_Flipbook_EN_(03_2022).pdf | PDF (6.56Mo)
-  → LE09457AH.pdf | PDF (8.17Mo)

CAD & Design specs / BIM

- Legrand_XL³-S_630_36_Modules_to_the_row.rfa | RFA (1.69Mo)
- Legrand_XL³-S_630_36_Modules_à_la_rangée.rfa | RFA (1.7Mo)

CATALOGUE PAGE & OTHERS

-  ex223001_0343.pdf | PDF (0.14Mo)
-  ex223001_0332.pdf | PDF (0.1Mo)

Agreements & Certificates

-  LOVAG-IT 18.129 | (0.57Mo)
-  LOVAG-IT 18.002 | (0.6Mo)
-  LOVAG-IT 18.130 | (0.56Mo)

-  LGRP-00471-V01.01-EN.pdf | PDF (1.01Mo)
-  LOVAG-IT 18.138 | (1.11Mo)
-  LOVAG-IT 17.083-R01 | (1.13Mo)