

Product sheet



LEGRAND

Flush-mounting cabinet Nedbox - transparent door - 3 rows - 36+6 modules

REF. 001453 | EAN. 3245060014537

> [Visit e-catalogue](#)

Product characteristics

- Flush-mounting cabinets Nedbox - 12 to 48 modules - IP 40 - IK 07 - Class II - Allows to achieve assemblies conform to IEC 61439 - 3 - Self extinguishing : resistance to incandescent wire 850°C
- Flush-mounting distribution cabinets - White RAL 9003 - Supplied with : - reversible door - screw terminal blocks for neutral and earth - Spacing between rails 125 mm - For installation in dry partitions use the flush-mounting kit Cat.No 0 014 90 With transparent door - Number of rows : 3 - Number of modules : 36 + 6 - Height : 555 mm - Width : 330 mm - Depth : 87 mm

Documentation

TECHNICAL DOCUMENTATION

→ [LE04724AA.pdf](#) | PDF (0.97Mo)

 [F02428EN_03.pdf](#) | PDF (0.57Mo)

 [F02428FR_03.pdf](#) | PDF (0.58Mo)

CAD & Design specs / BIM

[Legrand_Coffrets_modulaires_encastrés_Nedbox.rfa](#) | RFA (2.47Mo)

[Legrand_Flush-mounting_cabinets_Nedbox.rfa](#) | RFA (2.46Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_0311.pdf](#) | PDF (0.13Mo)

Agreements & Certificates

 [LGRP-00856-V01.01-EN.pdf](#) | PDF (0.6Mo)

 [LOVAG-IT 16.040](#) | (1.35Mo)