

Product sheet



LEGRAND

Sounder - IP42 - IK07 - 90 dB - 12/24/48 V= - white

REF. 040580 | EAN. 3245060405809

> [Visit e-catalogue](#)

Product characteristics


- Sounders, sounder beacons, bells, electromagnetic door holder and safety electrical power supplies
- Sounders - Conform to EN 54 - 3 standard and CE CPR approved - IP 42 - IK 07 - Surface - mounting - Sound level : 90 dB at 2 meters - NF S 32 - 001 sound - Voltage range : 10 - 58 V - Average consumption : 12 V DC 5 mA - 24 V DC 9 mA - 48 VDC 13 mA

Documentation

TECHNICAL DOCUMENTATION

→ [LE02619AB.pdf](#) | PDF (1.32Mo)

Agreements & Certificates

 [NFSSI Composant-DS 029 A2](#) | (0.26Mo)

 [LGRP-00272-V01.01-FR.pdf](#) | PDF (0.61Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_0921.pdf](#) | PDF (0.05Mo)