

Product sheet



LEGRAND

Microwaves IP40 ceiling-mounting DALI Lighting Management sensor for 1 circuit - 360° - 10.525 GHz

REF. 048956 | EAN. 3414971267404

> [Visit e-catalogue](#)

Product characteristics

- Lighting Management sensors for 1 circuit - Lighting Management sensors for passage areas with natural light - Check presence and natural light level continuously, switch off when there is sufficient natural light - Occupancy mode (automatic switch - on/off factory setting) - Can be used with push - button Cat.No 0 770 40 (or illuminated push - button Cat.No 0 770 33) for vacancy mode (manual switch - on and manual or automatic switch - off) - Precise on - site adjustment using configuration tool Cat.No 0 882 30 - Adjustable time delay : 5 s to 59 min - Light level threshold adjustable from 5 to 1275 lux
- Ideal for passage areas Microwaves IP 40 ceiling - mounting DALI Lighting Management sensor, 360° - DALI dimming sensors with a relay for switching an additional load - Maximum number of DSI or DALI ballasts : 10 (20 if the relay is disabled) - Microwaves detection, Front coverage of 6 x 30 m with head tilted to 80° - Consumption 0,96 W - Recommended installation height : 2.6 m - Can be installed on surface with dedicated installation box (Cat.No 0 489 64) - Microwaves admissible frequencies vary, select the correct product version according to your geographical region - 10,525 GHz

Documentation

CATALOGUE PAGE & OTHERS

 [ex223001_0891.pdf](#) | PDF (0.05Mo)

 [ex223001_0888.pdf](#) | PDF (0.07Mo)

CAD & Design specs / BIM

[Legrand_Gestion_eclairage_Detecteur_Presence_Plafond_autonome_R2.rfa](#) | RFA (2.17Mo)

[Legrand_Lighting_Management_Standalone_Presence_Sensor_Ceilin g_R2.rfa](#) | RFA (2.17Mo)

Agreements & Certificates

 [Decl. UE RED-DC0091](#) | (0.18Mo)