

Product sheet



LEGRAND

Sounder - IP65 - IK07 - 90 dB - 12/24/48 V= - red

REF. 040590 | EAN. 3245060405908

[> Visit e-catalogue](#)

Product characteristics

- Sounders, sounder beacons, bells, electromagnetic door holder and safety electrical power supplies
- Sounders - Conform to EN 54 - 3 standard and CE CPR approved - IP 65 - IK 07 - Surface - mounting - Sound level : 90 dB at 2 meters - NF S 32 - 001 sound - Voltage range : 10 - 42 V - Average consumption : 12 V 5 mA - 24 V 9 mA - 2 cable glands supplied

Documentation

TECHNICAL DOCUMENTATION

→ [LE02619AB.pdf](#) | PDF (1.32Mo)

Agreements & Certificates

 [LGRP-00276-V01.01-EN.pdf](#) | PDF (0.57Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_0921.pdf](#) | PDF (0.05Mo)