

# Product sheet



AXOLUTE BTICINO

Axolute - led lamp 12v blue

REF. BT-H4743/12B | EAN. 8005543567722

[> Visit e-catalogue](#)

## Product characteristics

- LED lamp designed for control circuit devices, suitable for industrial panel applications.
- Rated voltage range of 127V to 240V AC at both 50Hz and 60Hz, ensuring broad compatibility.
- Integrated voltage decreasing resistor and diode for enhanced circuit protection and reliability.
- IP55 degree of protection, providing robust resistance against dust and water ingress.
- Blue LED light source with screw connection, dimensions 50x55x50mm, operating temperature 5to40°C.

## Documentation

### TECHNICAL DOCUMENTATION

 IDP001636\_01-EN.pdf | PDF (0.3Mo)

### CATALOGUE PAGE & OTHERS

 BR LIVING NOW\_LEG4142.pdf | PDF (19.6Mo)

 ex223001\_0776.pdf | PDF (0.14Mo)