

# Product sheet



SYNERGY™ LEGRAND

Sinergy Sleek shaver socket Brushed Stainless steel

REF. 832090 | EAN. 3414970661142

> [Visit e-catalogue](#)

## Product characteristics

- Supply : 230V~ 50/60Hz Output : 230V~ or 120V~ - 20VA max
- Back box to be min. 45mm deep
- Conform to BS EN 61558
- Screwless cover plate is square 146x86 mm, product thickness is 4mm (once is installed onto the wall).
- Complete product, cover plates are clipped onto the mechanism itself.

## Recommendation / Restriction

- Recommended inside use only

## The product's benefits

### Installation

- Screwless live and neutral terminals

### Usage

- Ideal for Hotel, suitable for use European, British and Australian 2 pin plugs

### Advantages

- Plate in austenitic stainless steel Non magnetic Grade 304L
- Made in UK
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

## Documentation

### CATALOGUE PAGE & OTHERS

 [ex223001\\_0731.pdf](#) | PDF (0.09Mo)

### Agreements & Certificates

 [OC / CB-FR\\_709925](#) | (0.54Mo)