

Product sheet



SYNERGY™ LEGRAND

Synergy™ Sleek - shaver socket - Polished Stainless Steel

REF. 832290 | EAN. 3414970662347

> [Visit e-catalogue](#)

Product characteristics

- Supply : 230V~ 50/60Hz Output : 230V~ or 120V~ - 20VA max
- Back box to be min. 45mm deep
- Conform to BS EN 61558
- Screwless cover plate is square 146x86 mm, product thickness is 4mm (once is installed onto the wall).
- Complete product, cover plates are clipped onto the mechanism itself.

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- Screwless live and neutral terminals

Usage

- Ideal for Hotel, suitable for use European, British and Australian 2 pin plugs

Advantages

- Plate is made in ferritic Stainless Steel - Grade 430, with a chromium plating which bring a better rusting resistance and a nicer finish
- Made in UK
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

Documentation

CATALOGUE PAGE & OTHERS

 [ex223001_0731.pdf](#) | PDF (0.09Mo)

Agreements & Certificates

 [OC / CB-FR_709925](#) | (0.54Mo)